

## Blacklight BL368 Linear & Circline

F15W T5 BL368

0000090



### Range features

- Features
- BL368 tubes emit an upgraded highly concentrated radiation with peak around 368 nm. Flying insects eye sensitivity is generally at or near this frequency
- 100% improvement in effectiveness (at 368nm)
- Depreciation of UV-A output over time is significantly reduced (80% at 5000hrs of original 100 hour output)
- Performs longer and better throughout the insect season
- Same shape, structural and electrical characteristics and control circuits as standard T12,T8 or T5 tubes
- Applications
- Insect traps, insect attraction is strongly increased
- Restaurants, kitchens, food shops, supermarkets
- Diazo printing machines
- Photo Polymerisation
- Chemical processing
- Mineral detection
- Various technical applications
- Directions for use
- Maximum exposure limits are set by EN60335-2-59:1997 at an effective 1.0 milliWatt per metre squared (1.0 mW/m<sup>2</sup>) measured at a distance of 1 metre originally based on the recommendations of the National Radiological Protection Board in the UK. The irradiance value for a single BL368-lamp measured without reflector and/or fixture, in free air at 25 celsius, is varying between 0.2 and 0.4 mW/m<sup>2</sup> depending on the wattage



### PRODUCT OVERVIEW

Ordering number	0000090
Type	T5
EAN code	5410288000909
Watt (Nominal) (W)	15

## Blacklight BL368 Linear & Circline

F15W T5 BL368

0000090

### DATA TABLE

#### General data

<b>Ordering number</b>	0000090
<b>Type</b>	T5
<b>EAN code</b>	5410288000909
<b>Long description</b>	Features. BL368 tubes emit an upgraded highly concentrated radiation with peak around 368 nm. Flying insects eye sensitivity is generally at or near this frequency. 100% improvement in effectiveness (at 368nm). Depreciation of UV-A output over time is significantly reduced (80% at 5000hrs of original 100 hour output). Performs longer and better throughout the insect season. Same shape, structural and electrical characteristics and control circuits as standard T12,T8 or T5 tubes. Applications. Insect traps, insect attraction is strongly increased. Restaurants, kitchens, food shops, supermarkets. Diazo printing machines. Photo Polymerisation. Chemical processing. Mineral detection. Various technical applications. Directions for use. Maximum exposure limits are set by EN60335-2-59:1997 at an effective 1.0 milliWatt per metre squared (1.0 mW/m <sup>2</sup> ) measured at a distance of 1 metre originally based on the recommendations of the National Radiological Protection Board in the UK. The irradiance value for a single BL368-lamp measured without reflector and/or fixture, in free air at 25 celsius, is varying between 0.2 and 0.4 mW/m <sup>2</sup> depending on the wattage
<b>Product name</b>	F15W T5 BL368
<b>Sales pack quantity</b>	25

#### Electrical data

<b>Watt (Nominal) (W)</b>	15
<b>Current (A)</b>	0.310

#### Physical data

<b>Length base to base (mm) - A</b>	288.3
<b>Length base to pin Min-Max - B</b>	293.0-295.4
<b>Lamp Length (mm) - C/L</b>	302.5
<b>Lamp Diameter (mm) - D</b>	16

## Blacklight BL368 Linear & Circline

F15W T5 BL368

0000090

### TECHNICAL DRAWINGS

